




背面収納付き回転式全身ミラー 組立説明書



組立推奨人数:2人



使用アイテム:ドライバー





M6*16
A (x4)



M6*30全ねじボルト
B (x2)




M4
C (x1)



M8*180
D (x3)



M5
E (x1)





M6*16
A (x4)



M6*30全ねじボルト
B (x2)




M4
C (x1)



M8*180
D (x3)



M5
E (x1)





M6*16
A (x4)



M6*30全ねじボルト
B (x2)




M4
C (x1)



M8*180
D (x3)



M5
E (x1)





M6*16
A (x4)



M6*30全ねじボルト
B (x2)





M4
C (x1)



M8*180
D (x3)



M5
E (x1)



B



M6*16
A (x4)



M6*30全ねじボルト
B (x2)





M4
C (x1)



M8*180
D (x3)



M5
E (x1)



CAGUUU

\ Follow me /

お友達追加・フォローをお願いします!
各SNSにて商品やクーポン情報を配信中です。



LINE



Instagram

☆レビューも書いていただけると、大変励みになります☆